


The black brush strips can easily be replaced with colour brush strips; no tools are required.

Simply remove the mounting frame from the top of the desk or table and unscrew the 3 re-usable plastic rivets.

CONI mounting frame

#	
Large	
338.0205	Grey metallic (powder-coated, similar to RAL9006)
338.0206	Anthracite (powder-coated, similar to RAL7016)
911.001	White (powder-coated, similar to RAL9010)
911.003	Black (powder-coated, similar to RAL9005)
911.005	Stainless steel (ground)
Small	
338.0203	Grey metallic (powder-coated, similar to RAL9006)
338.0204	Anthracite (powder-coated, similar to RAL7016)
911.000	White (powder-coated, similar to RAL9010)
911.002	Black (powder-coated, similar to RAL9005)
911.004	Stainless steel (ground)





For suitable **power strips**, see from page 80.

CONI bracket

- · For mounting CONI power strips without using a mounting frame, can be installed e.g. under a tabletop in a cable tray. Standard chipboard screws (which can be purchased from all good retailers) are required for mounting.
- · The back-side outlet and bending radii of power and data connections are considered.
- · Material/surface: black steel sheet (powder-coated, similar to RAL9005)



918.002

CONI bracket, tallBlack | 2 items in plastic bag | Distance between floor and socket profile: 30 mm
Distance between floor and top edge of power strip: 74 mm



CONI holder

- · For optional mounting on CONI mounting frame
- \cdot Allows cable lengths to be stowed away when plugged in
- · Easy to fit by inserting into mounting frame (already fitted), using plastic rivets supplied
- · Small extra mounting depth of approx. 20 mm in addition to depth of mounting frame
- · Material/surface: black steel sheet (powder-coated, similar to RAL9005)





CONI brush strip

#	
Large CONI	brush strip
911.905	Red
911.906	Blue
911.907	White
911.908	Yellow
911.909	Black
Small CONI	brush strip
911.900	Red
911.901	Blue
911.903	Yellow
911.904	Black

